



www.vintageair.com

Reduced Barrier Binary Switch Kit with Beadlock (246791)

NOTE: This fitting must be installed in the high-pressure line between the condenser and drier or between the drier and evaporator.

1. Wire according to wiring diagram in Figure 1, below.




Figure 1

Packing List:

No.	Qty.	Part No.	Description
1.	1	11078-VUS	Binary Switch, Female
2.	1	348291	#6 Splicer with Safety Switch Port, Reduced Barrier

Checked By: _____
 Packed By: _____
 Date: _____

18865 Goll St. San Antonio, TX 78266
Phone: 800-862-6658
Sales: sales@vintageair.com
Tech Support: tech@vintageair.com
www.vintageair.com